

All Rosemarie masks are:

**ASTM Level 2
certified**



rosemarie
PRODUCTS COMPANY

Quality, unbeatable value, and impeccable branding™



RM Wellness Face Masks

09-27-20

We ship through
Emerson Healthcare



Emerson Logistics
A Consumer Products Logistics Solution

Carl Bradley – Rosemarie Products Co.
Steve Hatch – Rosemarie Products Co.

50ct RM Wellness Face Masks!

Cost is only
\$0.19 per mask!

50CT RM Wellness Ear Loop Face Mask



50-71083-40

50CT Carton
Cost: \$9.50

Cost per mask = \$0.19

Case pack = 40 cartons
Masks per case = 2,000

50CT RM Wellness Comfort Flex Face Mask



50-71073-40

50CT Carton
Cost: \$9.50

Cost per mask = \$0.19

Case pack = 40 cartons
Masks per case = 2,000

with Comfort Flex
Ear Loops

Understanding ASTM Levels

All Rosemarie masks are:

**ASTM Level 2
certified**

ASTM PERFORMANCE LEVELS	<p>ASTM LEVEL 3</p> <p>High Fluid Resistance 160 mmHg Filtration Efficiency BFE ≥ 98% PFE ≥ 98% @ 0.1 micron Breathability - Delta P < 5.0 mm H₂O/cm² Flame Spread Class 1</p>		<p>Ideal for procedures where heavy to moderate amounts of fluid, spray and/or aerosols are produced.</p> <p><i>Meets EN14683 Rating – Type IIR Standard.</i></p> <p style="text-align: right;"><small>Pictured: Ultra[®] Sensitive Earloop with Secure Fit[®] Mask Technology</small></p>	
	<p>ASTM LEVEL 2</p> <p>Moderate Fluid Resistance 120 mmHg Filtration Efficiency BFE ≥ 98% PFE ≥ 98% @ 0.1 micron Breathability - Delta P < 5.0 mm H₂O/cm² Flame Spread Class 1</p>		<p>Ideal for procedures where moderate to light amounts of fluid, spray and/or aerosols are produced.</p> <p><i>Meets EN14683 Rating – Type IIR Standard.</i></p> <p style="text-align: right;"><small>Pictured: Procedural Earloop with Secure Fit[®] Mask Technology</small></p>	
	<p>ASTM LEVEL 1</p> <p>Low Fluid Resistance 80 mmHg Filtration Efficiency BFE ≥ 95% PFE ≥ 95% @ 0.1 micron Breathability - Delta P < 4.0 mm H₂O/cm² Flame Spread Class 1</p>		<p>Ideal for procedures where low amounts of fluid, spray and/or aerosols are produced.</p> <p><i>Meets EN14683 Rating – Type II Standard.</i></p> <p style="text-align: right;"><small>Pictured: Isofluid[®] Earloop with Secure Fit[®] Mask Technology</small></p>	
	<p>LOW PERFORMANCE</p> <p>Surgical Molded Utility Mask Physical Barrier Only No LEVEL Performance Level ** Filtration Efficiency N/A</p> <p><small>**Unless mask manufacturer certifies mask meets ASTM performance Level 1</small></p>		<p>Ideal as a comfortable substitute for earloop face masks, this mask is a simple physical barrier for exams and visitations or for dry, short procedures that do not produce fluid, spray or aerosols.</p> <p style="text-align: right;"><small>Pictured: Surgical Molded</small></p>	
	<p>MINIMUM PERFORMANCE</p> <p>Utility Mask (Tissue/Tissue) Physical Barrier Only No LEVEL Performance Level Filtration Efficiency N/A</p>		<p>Ideal as a simple physical barrier for exams and visitations or for dry, short procedures that do not produce fluid, spray or aerosols.</p> <p style="text-align: right;"><small>Pictured: Isolite[®] Earloop</small></p>	



All Rosemarie face masks are ASTM Level 2 certified.



All our masks have 3-Layers of Protection

3-Layers of Protection

Layer 1: Leak-proof outer layer of spunbonded nonwoven fabric isolates dust and droplets

Layer 2: Melt-blown nonwoven, high-density BFE95 (Bacterial Filtration Efficiency) inner layer filters $\geq 95\%$ micro particles

Layer 3: Direct skin contact layer of spunbonded nonwoven Fabric absorbs moisture

Leak Proof Nonwoven Fabric

High Density Filter Layer

Direct Contact Skin Layer

Comfort Flex Ear Loops

For Non-surgical Use. Single Use Only.

Special note about Comfort Flex Face masks:

- If employees are going to wear masks most of the day, we recommend our Comfort Flex Face Masks.
- They have wide fabric ear loops that do not irritate the back of the ear.